

PHILIPS

Smart LED RGB A80
Bulb, E27 Base, 2452 lm

Smart LED

Millions of colours

Tunable white light

Low dimming

Control with WiZ app or voice

8719514437319



Make your home lighting smarter

Transform your space with smart lighting that adapts to every moment. Set the mood with bright light in millions of colours, as well as preset modes like Fireplace and Ocean. Easily switch between cool, energising white light and warm, relaxing tones with a tunable range from 2,200 K to 6,500 K, and fine-tune the brightness from 100% down to just 1% for complete control.

Smart control

- Connected by WiZ
- Smart controls

Smart features

- SpaceSense motion detection

Smart devices


- Matter-certified

Light modes

- Millions of colours
- Tunable white light
- Low dimming

Highlights

Connected by WiZ



Control your lights using the WiZ app, accessories or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Matter-certified




Control it your way using your preferred smart home assistant – Matter-compatible for seamless integration with Alexa, Google Home and Apple Home.

Low dimming



Dim your light smoothly from full brightness down to 1% to achieve the right level of light for whatever you're doing.

Smart controls




Control your lights using the WiZ app, accessories or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Millions of colours



Choose any light colour from the palette or apply a preset light mode, like Fireplace or Ocean, to create an amazing atmosphere and set the mood.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so they switch on automatically when you enter the room – all you need are two or more Connected by WiZ lights or devices.

Tunable white light



Easily adjust from cool, bluish hues that enhance visibility and focus to soft, warmer tones for relaxing in the evening (CCT range 2,200 K–6,500 K).

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: A80
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Dimmable: Yes

Lamp dimensions

- Weight: 0.3 kg

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.

- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics

- Colour consistency: 6 SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2200–6500 K
- Light Colour Category: Full colour
- Nominal luminous flux: 2452 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Luminous efficacy (rated) (nom.): 132

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 140 mA

Packaging information

- EAN: 8719514437319
- EOC: 871951443731900
- Product title: PHI WFB 150W A80 E27 922-65 RGB 1PF/6

Power consumption

- Power factor: 0.5
- Voltage: AC 220–240 V
- Wattage equivalent: 150 W
- Energy efficiency label (EEL): E
- Power: 18.5 W
- Energy consumption kWh/1,000 hours: 19

Product dimensions and weight

- Overall height: 16.3 mm
- Overall length: 16.3 mm
- Overall width: 8.3 mm

Rated values

- Rated lifetime: 15,000
- Rated luminous flux: 2452 lm
- Rated power: 18.5 W

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50–60
- Bulb technology: LED
- EPREL Registration Number: 1901103
- Flux measurement reference: Sphere

The bulb

- Software upgradable: Yes

What's supported

- Compatible with Effects feature: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum 60 months from date of purchase from an authorised reseller
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with third-party systems: Alexa, Google Home, Homey, IFTTT, Matter, Samsung SmartThings, Siri Shortcuts
- Matter functionality: Via third-party hubs (Wi-Fi)

Packaging dimensions and weight

- EAN/UPC - product: 8719514437319
- Net weight: 0.22 kg
- Gross weight: 0.31 kg
- Height: 21.6 cm
- Length: 10.5 cm
- Width: 10.7 cm



Issue date: 2026-08-05
Version: 0.331

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com