

# PHILIPS

## Downlight

Functional

StylEdge

White

10W, Round

8718699631550



## Superior light and style

Decorative downlight made with high quality aluminium which blends well on your ceiling enhancing the décor.

### Match your interior

- Decorative metallic finishing

### Light effect

- Bright light with uniform distribution
- Durable synthetic diffuser for uniform light and reduced glare

### Material & finishing

- Durable aluminum housing

### Durability

- Long life span up to 30,000 hours

# Highlights

## Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

## Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Durable synthetic diffuser for uniform light and reduced glare

Provides a soft glow for relaxation and focus without distracting glare.

## Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

## Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: White
- Material: Metal

## Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 10,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

## Light characteristics

- Beam angle: 120
- Color consistency: 5 SDCM
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Warm-up time to 60% light: 2
- Luminous Efficacy (rated) (Nom): 90

## Miscellaneous

- Especially designed for: Living Room

## Other characteristics

- Lamp current: 50 mA

## Power consumption

- Power factor: 0.9
- Voltage: 220-240 V

## Product dimensions and weight

- Net weight: 0.13 kg
- Overall height: 47 mm
- Overall length: 121 mm
- Overall width: 121 mm
- Recessed Ceiling cutout: 11.0 cm x 11.0 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Diameter: 121 mm
- Total lumen output fixture: 900
- Bulb technology: LED
- Mains power: 220-240
- Fixture dimmable: No
- Wattage bulb included: 10
- IP code: IP20
- Class of protection: Class II - Double Insulated

## The bulb

- Software upgradable: No

#### What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

#### Packaging dimensions and weight

- EAN/UPC – product: 8718699631550
- Net weight: 0.14 kg
- Gross weight: 0.19 kg
- Height: 14.5 cm
- Length: 16.5 cm
- Width: 5.2 cm



Issue date: 2026-08-05  
Version: 0.223

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)