PHILIPS

Smart LED
RGB Filament ST19 E 00 lm

Smart LED

Decorative bulb

Millions of colors

Tunable white light

Control with app or voice

046677582821

Make your home lighting smarter

This decorative LED bulb combines timeless style with advanced smart lighting features, making it a standout addition to any space. The visible filament design creates a warm, eye-catching focal point that enhances your room's atmosphere even when switched off, while offering millions of color options and preset modes like Fireplace or Ocean to instantly set the perfect mood.

Smart control
- Connected by WiZ
- Smart controls

Smart features
- SpaceSense motion detection

Light modes
- Millions of colors
- Decorative bulb
- Tunable white light
- Low dimming

Highlights

Connected by WiZ

Control your lights using the WiZ app, accessories, or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Millions of colors

Choose any light color from the palette or apply a preset light mode, like Fireplace or Ocean, to create an amazing atmosphere and set the mood.

Low dimming



Dim your light smoothly from full brightness down to 1% to achieve the right level of light for whatever you're doing.

Smart controls



Control your lights using the WiZ app, accessories, or voice commands via your smart home assistant; compatible with Alexa and Google Home.

Decorative bulb

The visible filament creates a warm, decorative focal point that enhances a room's atmosphere even when the light is switched off.

SpaceSense motion detection



Turn your lights into motion sensors using integrated SpaceSense technology, so that they switch on automatically when you enter the room—all you need are two or more Connected by WiZ lights or devices.

Tunable white light

Easily adjust from cool, bluish hues that enhance visibility and focus to soft, warmer tones for relaxing in the evening

Specifications

Bulb characteristics
- Intended use: Indoor
- Lamp shape: ST19
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear
- Dimmable: Yes

Bulb dimensions
- Weight: 0.055 kg

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 20,000
- Nominal lifetime: 15,000

Extra feature/accessory incl.
- LED integrated: Yes
- Solar Energy: No
- Warm glow dimmable light: No

Light characteristics
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 1800-2100 K
- Light Color Category: Full color
- Nominal luminous flux: 300 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Luminous Efficacy (rated) (Nom): 47

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Lamp current: 75 mA

Packaging information
- EAN: 046677582821
- EOC: 582825
- Product title: 6.3ST19/Wi-Fi BLE Color CL 4/1PF

Power consumption
- Power factor: 0.7
- Voltage: AC 120 V
- Wattage equivalent: 25 W
- Power: 6.3 W

Product dimensions and weight
- Overall height: 9/16 inch
- Overall length: 9/16 inch
- Overall width: 1/4 inch

Rated values
- Rated lifetime: 15,000
- Rated luminous flux: 300 lm
- Rated power: 6.3 W

Service
- Warranty: 3 year(s)

Technical specifications
- Frequency: 60
- Bulb technology: LED

The bulb
- Software upgradable: Yes

What's supported
- Compatible with Effects: Yes
- WiFi: 802.11b/g/n
- Defined support period: Minimum 60 months from date of purchase from an authorized reseller
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android
- Communication protocol: Bluetooth, WiFi (2.4GHz)
- Compatibility with 3rd party systems: Alexa, Enki, Google Home, Homey, IFTTT, Matter, Samsung Smartthings, Siri Shortcuts
- Matter functionality: Via 3rd party hubs (Wi-Fi)

Packaging dimensions and weight
- EAN/UPC - product: 046677582821
- Net weight: 0.05 kg
- Gross weight: 0.11 kg
- Height: 19 cm
- Length: 9.9 cm
- Width: 7.2 cm

046677582821

Issue date: 2026-08-05
Version: 0.185

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com