

PHILIPS

ProjectLine Wrap
Batten40/33/29W


Battens

3500/4000/5000K

White

MultiColor Temperature

046677607401



One fixture. Your switch. Three light settings.

Great linear solution for garage, workshop and basement, which includes Multi-CCTs and multi-lumens features

Easy installation

- Installation couldn't be simpler. Integrated clips on both sides of the fixture hold it in place, so no screw mounting is necessary. A GU10 connector cable makes it easy to attach a bulb.

Durability

- Long life span up to 50,000 hours

Three brightness levels


- The Philips Cilantro spotlight works with your existing light switch, so you can easily toggle between its three brightness levels without having to install a dimmer.

Highlights

Easy to install

Installation couldn't be simpler. Integrated clips on both sides of the fixture hold it in place, so no screw mounting is necessary. A GU10 connector cable makes it easy to attach a bulb.

Long life span up to 50,000 hours



Philips LED technology extends your product's lifetime up to 50,000 hours.

Three brightness levels

The Philips Cilantro spotlight works with your existing light switch, so you can easily toggle between its three brightness levels without having to install a dimmer.

Specifications

Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

Design and finishing

- Color: White
- Material: Metal

Durability

- Number of switch cycles: 25,000
- Nominal lifetime: 50,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: No
- Remote control included: No

Light characteristics

- Beam angle: 110
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80
- Color temperature: 3500/4000/5000
- Warm-up time to 60% light: <2
- Luminous Efficacy (rated) (Nom): 115

Miscellaneous

- Especially designed for: Kitchen, Garage, Home Office
- Style: Contemporary
- Type: Battens
- EyeComfort: No
- Extra Features: MultiColor Temperature

Other characteristics

- Lamp current: 120V:333, 277V:144 mA

Power consumption

- Power factor: 0.9

Product dimensions and weight

- Net weight: 1.79 kg
- Height: 2-3/8 inch
- Length: 48-1/16 inch
- Width: 5-9/16 inch

Service

- Warranty: 3 year(s)

Technical specifications

- Total lumen output fixture: 4600/3800/3340
- Bulb technology: LED
- Light color: Tunable white light
- Mains power: AC 120-277
- Wattage bulb included: 40/33/29
- Class of protection: Class II - Double Insulated
- Number of light sources: 1
- UL Wet/ damp/ dry location: Damp location

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC – product: 046677607401
- Net weight: 3.58 kg
- Gross weight: 3.8 kg
- Height: 17.1 cm
- Length: 15.4 cm
- Width: 129.7 cm



Issue date: 2026-08-05
Version: 0.136

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com