

Jagg Table Lamp

TCTLJA



Jagg – Table lamp in Grey and Transparent

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

Benefits

- Circular design
- Low weight and easy to install
- Sustainably 3D printed

Applications

- Hospitality
- Residential

Features

- Color options: Transparent and Grey
- Light Source: E27 LED bulb (not included)
- Wattage: Compatible with E27 bulbs up to 8W
- Installation: Type-C plug

Versions

Jagg Ribbed Transparent 2



Jagg Ribbed Grey 5





Jagg Ribbed Grey 2



Jagg Ribbed Transparent 5





Dimensional drawing



DL F02 TL E27 SF GR000 CL BK402 FEU

DL F05 TL E27 SF GR000 CL BK402 FEU



DL F02 TL E27 SF CL000 CL BK402 FEU

DL F05 TL E27 SF CL000 CL BK402 FEU

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
912500109318	DL F02 TL E27 SF CL000 CL BK402 FEU	Transparent
912500109508	DL F05 TL E27 SF GR000 CL BK402 FEU	Gray
912500109317	DL F02 TL E27 SF GR000 CL BK402 FEU	Gray
912500109509	DL F05 TL E27 SF CL000 CL BK402 FEU	Transparent