



Lantern – Table lamp in two colors and textures

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

Benefits

- Circular design
- Low weight and easy to install
- Sustainably 3D printed

Applications

- Hospitality
- Residential

Features

- Color and texture options: Two colors and textures
- Light Source: E27 LED bulb (not included)
- Wattage: Compatible with E27 bulbs up to 8W
- Installation: Type-C plug

Versions

Lantern T404 White 2



Lantern T304 Transparent 2





Lantern T404 White 1



Lantern T304 Transparent 1




Dimensional drawing




DL L1L TL E27 T304CL000 BK402 FEU

DL L2L TL E27 T304CL000 BK402 FEU



DL L2L TL E27 T404WH300 BK402 FEU



DL L1L TL E27 T404WH300 BK402 FEU

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
912500109512	DL L2L TL E27 T404WH300 BK402 FEU	White
912500109514	DL L2L TL E27 T304CL000 BK402 FEU	Transparent
912500109319	DL L1L TL E27 T404WH300 BK402 FEU	White
912500109513	DL L1L TL E27 T304CL000 BK402 FEU	Transparent