

Voila Table Lamp

TCTLVO



Voila – Table Lamp in different colors

Looking for a stylish table lamp that is not only functional but also adds a touch of modernity to your space? Look no further than the Design Award winning Voila Table Lamp. With this lamp, our designers reimagined the classic table lamp. The design has a familiar iconic silhouette with innovative textures on the surface giving it a distinctive look and feel and making each lamp in this family special.

Benefits

- Circular design
- Low weight and easy to install
- Sustainably 3D printed

Applications

- Hospitality
- Residential

Features

- Color and Texture Options: Various combinations available
- Light Source: E27 LED bulb (not included)
- Wattage: Compatible with E27 bulbs up to 8W
- Installation: Type-C plug

Versions

Voila T204 Brass



Voila T309 Brass



Voila T309 White



Voila T204 Transparent



Voila T204 Bronze



Voila T309 Transparent



Voila T309 Green



Voila T204 Pink





Voila T204 Beige



Voila T309 Pink



Voila T309 Bronze



Voila T309 Beige




Voila T204 White




Voila T204 Green


Dimensional drawing




DL V1T TL E27 OT204CL000 AT204CL000 FEU




DL V1T TL E27 OT204WH300 AT204WH300 FEU




DL V1T TL E27 OT309PK400 AT309PK400 FEU




DL V1T TL E27 OT309BR401 AT309BR401 FEU




DL V1T TL E27 OT309CL000 AT309CL000 FEU




MC V1T TL E27 OT309BS410 AT309BS410 FEU




DL V1T TL E27 OT204PK400 AT204PK400 FEU




DL V1T TL E27 OT204BZ410 AT204BZ410 FEU




DL V1T TL E27 OT309GN402 AT309GN402 FEU




DL V1T TL E27 OT309WH300 AT309WH300 FEU




DL V1T TL E27 OT204GN402 AT204GN402 FEU



MC V1T TL E27 OT204BR401 AT204BR401 FEU



DL V1T TL E27 OT309BZ410 AT309BZ410 FEU



DL V1T TL E27 OT204BS410 AT204BS410 FEU

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
912500109505	DL V1T TL E27 OT204BS410 AT204BS410 FEU	Brass
912500109096	MC V1T TL E27 OT309BS410 AT309BS410 FEU	Brass
912500109316	DL V1T TL E27 OT309WH300 AT309WH300 FEU	White
912500109506	DL V1T TL E27 OT204CL000 AT204CL000 FEU	Transparent
912500109504	DL V1T TL E27 OT204BZ410 AT204BZ410 FEU	Bronze

Order Code	Full Product Name	Housing Color
912500109501	DL V1T TL E27 OT309CL000 AT309CL000 FEU	Transparent
912500109315	DL V1T TL E27 OT309GN402 AT309GN402 FEU	Satin Sage (GN402)
912500109502	DL V1T TL E27 OT204PK400 AT204PK400 FEU	Pink
912500109095	MC V1T TL E27 OT204BR401 AT204BR401 FEU	Beige
912500109498	DL V1T TL E27 OT309PK400 AT309PK400 FEU	Pink
912500109499	DL V1T TL E27 OT309BZ410 AT309BZ410 FEU	Bronze
912500109314	DL V1T TL E27 OT309BR401 AT309BR401 FEU	Beige
912500109507	DL V1T TL E27 OT204WH300 AT204WH300 FEU	White
912500109503	DL V1T TL E27 OT204GN402 AT204GN402 FEU	Satin Sage (GN402)