

Jagg Table Lamp

TCTLJA



Jagg – Table lamp in Grey and Transparent

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

Benefits

- Circular design
- Low weight and easy to install
- Sustainably 3D printed

Applications

- Hospitality
- Residential

Features


- Color options: Transparent and Grey
- Light Source: E27 LED bulb (not included)
- Wattage: Compatible with E27 bulbs up to 8W
- Installation: Type-C plug

Versions

Jagg Ribbed Transparent 5



Dimensional drawing



DL F05 TL E27 SF CL000 CL BK402 FEU

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Housing Color	Transparent
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes