



## Voila – Table Lamp in different colors

Looking for a stylish table lamp that is not only functional but also adds a touch of modernity to your space? Look no further than the Design Award winning Voila Table Lamp. With this lamp, our designers reimagined the classic table lamp. The design has a familiar iconic silhouette with innovative textures on the surface giving it a distinctive look and feel and making each lamp in this family special.

### General Information

|                 |         |
|-----------------|---------|
| Warranty period | 5 years |
|-----------------|---------|

### Operating and Electrical

|                      |                 |
|----------------------|-----------------|
| Input Voltage        | 220 to 240 V    |
| Line Frequency       | 50 to 60 Hz     |
| Protection class IEC | Safety class II |

### Mechanical and Housing


|                  |                              |
|------------------|------------------------------|
| Housing Material | 3D printed, GN402 Satin Sage |
| Housing Color    | Satin Sage (GN402)           |
| Overall length   | 215 mm                       |
| Overall width    | 215 mm                       |
| Overall height   | 301 mm                       |
| Overall diameter | 215 mm                       |

|                                     |                         |
|-------------------------------------|-------------------------|
| Dimensions (Height x Width x Depth) | 301 x 215 x 215 mm      |
| Nominal Ceiling cut-out diameter    | 215 mm                  |
| Nominal ceiling cut-out length      | 215 mm                  |
| Nominal ceiling cut-out width       | 215 mm                  |
| Ingress protection code             | IP20 [Finger-protected] |
| Mech. impact protection code        | IK02 [0.2 J standard]   |
| Net Weight (Piece)                  | 0.548 kg                |
| Cable color                         | transparent             |

## Approval and Application

|                   |                                   |
|-------------------|-----------------------------------|
| Glow-wire test    | Temperature 650 °C, duration 30 s |
| CE mark           | Yes                               |
| EU RoHS compliant | No                                |

## Dimensional drawing



## Product Data

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Order product name              | DL V1T TL E27 OT309GN402 AT309GN402 FEU |
| Full product name               | DL V1T TL E27 OT309GN402 AT309GN402 FEU |
| Full product code               | 872016986990500                         |
| Order code                      | 912500109315                            |
| Material Nr. (12NC)             | 912500109315                            |
| Numerator - Quantity Per Pack   | 1                                       |
| EAN/UPC - Product/Case          | 8720169869905                           |
| Numerator - Packs per outer box | 1                                       |
| EAN/UPC - Case                  | 8720169869905                           |