



Jagg – Table lamp in Grey and Transparent

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

General Information

Warranty period	5 years
-----------------	---------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing


Housing Material	3D printed, GR000 Transparent Smokey
Housing Color	Gray
Overall length	220 mm
Overall width	220 mm
Overall height	240 mm
Overall diameter	220 mm

Dimensions (Height x Width x Depth)	240 x 220 x 220 mm
Nominal Ceiling cut-out diameter	220 mm
Nominal ceiling cut-out length	220 mm
Nominal ceiling cut-out width	220 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.089 kg
Cable color	transparent

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	No

Dimensional drawing



Product Data

Order product name	DL F02 TL E27 SF GR000 CL BK402 FEU
Full product name	DL F02 TL E27 SF GR000 CL BK402 FEU
Full product code	872016986992900
Order code	912500109317
Material Nr. (12NC)	912500109317
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169869929
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169869929