



Lantern – Table lamp in two colors and textures

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

General Information

Warranty period	5 years
-----------------	---------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing


Housing Material	3D printed, WH300 Satin Translucent White
Housing Color	White
Overall length	200 mm
Overall width	200 mm
Overall height	218 mm
Overall diameter	200 mm

Dimensions (Height x Width x Depth)	218 x 200 x 200 mm
Nominal Ceiling cut-out diameter	200 mm
Nominal ceiling cut-out length	200 mm
Nominal ceiling cut-out width	200 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.548 kg
Cable color	transparent

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	No

Dimensional drawing



Product Data

Order product name	DL L1L TL E27 T404WH300 BK402 FEU
Full product name	DL L1L TL E27 T404WH300 BK402 FEU
Full product code	872016986994300
Order code	912500109319
Material Nr. (12NC)	912500109319
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169869943
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169869943