



Voila – Table Lamp in different colors

Looking for a stylish table lamp that is not only functional but also adds a touch of modernity to your space? Look no further than the Design Award winning Voila Table Lamp. With this lamp, our designers reimagined the classic table lamp. The design has a familiar iconic silhouette with innovative textures on the surface giving it a distinctive look and feel and making each lamp in this family special.

General Information

Warranty period	5 years
-----------------	---------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Housing Material	3D printed, BZ410 Satin Bronze
Housing Color	Bronze
Overall length	215 mm
Overall width	215 mm
Overall height	301 mm
Overall diameter	215 mm

Dimensions (Height x Width x Depth)	301 x 215 x 215 mm
Nominal Ceiling cut-out diameter	215 mm
Nominal ceiling cut-out length	215 mm
Nominal ceiling cut-out width	215 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.548 kg
Cable color	transparent

Product Data

Order product name	DL V1T TL E27 OT309BZ410 AT309BZ410 FEU
Full product name	DL V1T TL E27 OT309BZ410 AT309BZ410 FEU
Full product code	872016987185400
Order code	912500109499
Material Nr. (12NC)	912500109499
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169871854
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169871854

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	No

Dimensional drawing

