



Shell – Table lamp in different textures

Place the Shell table lamp as a wall washer with the light facing the wall for an illuminated wall. The transparent material makes the whole lamp appear to glow which increases the light output in an atmospheric way. This minimalist lamp resembling eggshell creates a beautiful base in your space. Natural light with a soft, friendly look.

General Information

Warranty period	5 years
-----------------	---------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing

Housing Material	3D printed, CL000 Clear
Housing Color	Transparent
Overall length	194 mm
Overall width	194 mm
Overall height	225 mm
Overall diameter	194 mm

Dimensions (Height x Width x Depth)	225 x 194 x 194 mm
Nominal Ceiling cut-out diameter	194 mm
Nominal ceiling cut-out length	194 mm
Nominal ceiling cut-out width	194 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.495 kg
Cable color	transparent

Product Data

Order product name	DL S1S TL E27 OT101CL000 IT101WH300 FEU
Full product name	DL S1S TL E27 OT101CL000 IT101WH300 FEU
Full product code	872016987195300
Order code	912500109510
Material Nr. (12NC)	912500109510
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169871953
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169871953

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	No

Dimensional drawing

