



Jagg – Table lamp in Grey and Transparent

Give this table lamp any place and your space suddenly gets a totally different look. With its extravagant ribbed structure, the lamp gives a unique “broken” and atmospheric lighting effect. With her elegant oval or wavy shapes, she is undoubtedly an asset within multiple interior styles. Jagg is available in 2 different variants and 2 different colors.

General Information

Warranty period	5 years
-----------------	---------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Protection class IEC	Safety class II

Mechanical and Housing


Housing Material	3D printed, CL000 Clear
Housing Color	Transparent
Overall length	175 mm
Overall width	175 mm
Overall height	220 mm
Overall diameter	175 mm

Dimensions (Height x Width x Depth)	220 x 175 x 175 mm
Nominal Ceiling cut-out diameter	175 mm
Nominal ceiling cut-out length	175 mm
Nominal ceiling cut-out width	220 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.089 kg
Cable color	transparent

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	Yes
EU RoHS compliant	No

Dimensional drawing



Product Data

Order product name	DL F05 TL E27 SF CL000 CL BK402 FEU
Full product name	DL F05 TL E27 SF CL000 CL BK402 FEU
Full product code	872016987194600
Order code	87194600
Material Nr. (12NC)	912500109509
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169871946
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169871946