



## Jewels Pendant – Smokey Grey & Water Blue

The Jewels Pendant is a statement of modern luxury, designed to transform light into an elegant and atmospheric experience. With its distinctive sculptural shape and refined detailing, this pendant brings a bold yet sophisticated presence to any commercial space. Its double-layered construction and rich reflective texture create a unique interplay of light and depth, while the transparent finish with a chic accent ensures a polished, high-end look. The result is a striking lighting piece that enhances both residential and commercial spaces with a warm, contemporary ambiance. The Jewels Pendant is available in two carefully crafted material options: Smokey Grey – A timeless, elegant finish with a deep, translucent tone and glass-like appearance, adding subtle luxury and sophistication to your space. Water Blue – Crafted from repurposed water jug materials, this sustainable version features soft translucent hues and a texture, offering a unique aesthetic while reducing environmental impact.

## General Information

|                 |         |
|-----------------|---------|
| Warranty period | 5 years |
|-----------------|---------|

## Operating and Electrical

|                      |                 |
|----------------------|-----------------|
| Input Voltage        | 220 to 240 V    |
| Line Frequency       | 50 to 60 Hz     |
| Protection class IEC | Safety class II |

## Mechanical and Housing

|                                     |                         |
|-------------------------------------|-------------------------|
| Housing Material                    | Polycarbonate           |
| Housing Color                       | Gray                    |
| Overall length                      | 202 mm                  |
| Overall width                       | 202 mm                  |
| Overall height                      | 309 mm                  |
| Dimensions (Height x Width x Depth) | 309 x 202 x 202 mm      |
| Ingress protection code             | IP20 [Finger-protected] |
| Mech. impact protection code        | IK02 [0.2 J standard]   |

|                    |          |
|--------------------|----------|
| Net Weight (Piece) | 0.726 kg |
| Cable color        | black    |

## Approval and Application

|                         |                                   |
|-------------------------|-----------------------------------|
| Energy Efficiency Class | n/a                               |
| Glow-wire test          | Temperature 650 °C, duration 30 s |
| CE mark                 | Yes                               |
| EU RoHS compliant       | No                                |

## Product Data

|                                 |                                           |
|---------------------------------|-------------------------------------------|
| Order product name              | DL J1S PS E27 OT101GR000<br>ABS410 FBK BK |
| Full product name               | DL J1S PS E27 OT101GR000<br>ABS410 FBK BK |
| Full product code               | 872016986587700                           |
| Order code                      | 86587700                                  |
| Material Nr. (12NC)             | 912500108936                              |
| Numerator - Quantity Per Pack   | 1                                         |
| EAN/UPC - Product/Case          | 8720169865877                             |
| Numerator - Packs per outer box | 1                                         |
| EAN/UPC - Case                  | 8720169865877                             |

## Dimensional drawing



