



## Cloak Pendant

Inspired by the layered fabrics of fashion, Cloak is a bulb-based pendant designed by Basten Leijh that offers flexibility and individuality in design. Each pendant has two adjustable belts that can be positioned to your preference. The outer belt offers two lighting styles: the white translucent belt provides a gentle glow, and the colored opaque belts create a layered lighting effect. These lamps are lightweight and easy to install in any setting. Moreover, the 3D printed parts of the pendant are made from at least 65% recycled or bio-circular materials, which makes it an eco-friendly choice for those who want to reduce their carbon footprint. Whether you're looking to create a cozy atmosphere in your living room or add some style to a commercial space, this pendant is a versatile lighting solution to meet your needs.

### General Information

|                 |         |
|-----------------|---------|
| Warranty period | 5 years |
|-----------------|---------|

### Operating and Electrical

|                |             |
|----------------|-------------|
| Input Voltage  | 220-240 V   |
| Line Frequency | 50 to 60 Hz |

Protection class IEC

Safety class II

## Approval and Application

Glow-wire test

Temperature 650 °C, duration  
30 s

CE mark

Yes

EU RoHS compliant

No

## Mechanical and Housing

|                                     |                                           |
|-------------------------------------|-------------------------------------------|
| Housing Material                    | 3D printed, WH300 Satin Translucent White |
| Housing Color                       | White                                     |
| Overall length                      | 206 mm                                    |
| Overall width                       | 206 mm                                    |
| Overall height                      | 212 mm                                    |
| Overall diameter                    | 206 mm                                    |
| Dimensions (Height x Width x Depth) | 212 x 206 x 206 mm                        |
| Nominal Ceiling cut-out diameter    | 206 mm                                    |
| Nominal ceiling cut-out length      | 206 mm                                    |
| Nominal ceiling cut-out width       | 206 mm                                    |
| Ingress protection code             | IP20 [Finger-protected]                   |
| Mech. impact protection code        | IK02 [0.2 J standard]                     |
| Mounting                            | Suspended                                 |
| Net Weight (Piece)                  | 0.895 kg                                  |
| Cable color                         | white                                     |

## Product Data

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Order product name              | TCPL00 S BS410 T101 WH T WH E27 N |
| Full product name               | TCPL00 S BS410 T101 WH T WH E27 N |
| Full product code               | 872016986930100                   |
| Order code                      | 86930100                          |
| Material Nr. (12NC)             | 912500109258                      |
| Numerator - Quantity Per Pack   | 1                                 |
| EAN/UPC - Product/Case          | 8720169869301                     |
| Numerator - Packs per outer box | 1                                 |
| EAN/UPC - Case                  | 8720169869301                     |

## Dimensional drawing

