

PHILIPS

Bulb 7W G95 B22
2700K NonDim

LED

2700K

806lm

15000h

8718696732441



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your clear incandescent bulbs.

High quality light

- No visible flicker

Choose a simple replacement for your old bulbs

- Similar shape and size as incandescent globe

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Replaces globe incandescent



With its beautifully shaped design and familiar dimensions, this is a contemporary lighting LED globe. The perfect sustainable replacement for traditional incandescent globes.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: B22
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 150
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: 0.5
- Color Code: 827 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700
- Luminous Flux: 806 lm
- Luminous Efficacy (rated) (Nom): 115

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718696732441
- EOC: 871869673244100
- Product title: LEDGlobe 7-60W G95 B22 WW 230V_AU

Power

- Power Factor (Fraction): 0.7

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage equivalent: 60
- Power: 7
- Energy Consumption kWh/1000 h: 7

Product dimensions and weight

- Overall height: 135 mm
- Overall length: 135 mm
- Overall width: 95 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50-60
- Diameter: 95 mm
- Bulb technology: LED
- Dimmable: No
- Cap-Base: B22

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC - product: 8718696732441
- Net weight: 0.11 kg
- Gross weight: 0.15 kg
- Height: 12.9 cm
- Length: 9.6 cm
- Width: 9.6 cm



Issue date: 2026-08-05
Version: 0.237

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com