

PHILIPS

Spot 120W R7S R7S

LED

3000K


2000 lm

15000 h

Dimming



8718699773694



Dimmable linear LED light with a 300-degree beam

This innovative Linear LED is the perfect replacement for halogen R7S bulbs, while far surpassing them in terms of energy efficiency.

High-quality light

- Cool, energising light

Highlights

3500K [LED Lamps]



This bulb has a colour temperature of 3,500 K providing you with a cool, energising light, perfect for creating an inviting ambiance to host friends or wind down with a book.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: R7s
- Lamp Finish: Clear
- Dimmable: Yes
- Bulb material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 3000 K
- Nominal luminous flux: 2000 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 830 | CCT of 3000K
- Luminous efficacy (rated) (nom.): 142

Miscellaneous

- EyeComfort: No
- Extra Features: Dimmable

Packaging information

- EAN: 8718699773694
- EOC: 871869977369400
- Product title: LED 120W R7S 118mm WH D RF 1PF/12

Power consumption

- Power factor: 0.8
- Voltage: 220-240 V
- Wattage equivalent: 120
- Energy efficiency label (EEL): D
- Power: 14
- Energy consumption kWh/1,000 hours: 14

Product dimensions and weight

- Overall height: 118 mm
- Overall length: 118 mm
- Overall width: 29 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- IP code: IP20
- EPREL Registration Number: 397582

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

[LED 120W R7S 118mm WH D SRT4]

- EAN/UPC - product: 8718699773694
- Net weight: 0.09 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm

Packaging dimensions and weight

[LED 120W R7S 118mm WH D RF 1PF/12]

- EAN/UPC - product: 8718699773694
- Net weight: 0.09 kg
- Gross weight: 0.11 kg
- Height: 14.6 cm
- Length: 3 cm
- Width: 6.3 cm



Issue date: 2026-08-05
Version: 0.521

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com