

PHILIPS

Candle 25 W P45
B22

LED

2700K

250 lm

15000 h



8719514309487



State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: B22
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 250 lm
- Warm-up time to 60% light: 0.5
- Colour Code: 827 | CCT of 2700K
- Luminous efficacy (rated) (nom.): 89

Miscellaneous

- EyeComfort: Yes

Packaging information

- EAN: 8719514309487
- EOC: 871951430948700
- Product title: LED 25W P45 B22 WW FR ND 1SRT4

Power consumption

- Power factor: 0.41
- Voltage: 220-240 V
- Wattage equivalent: 25
- Energy efficiency label (EEL): F
- Power: 2.8
- Energy consumption kWh/1,000 hours: 3

Product dimensions and weight

- Overall height: 85 mm
- Overall length: 85 mm
- Overall width: 45 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50-60
- Bulb technology: LED
- EPREL Registration Number: 453222

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8719514309487
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 12.7 cm
- Length: 4.6 cm
- Width: 6.3 cm



Issue date: 2026-08-05
Version: 0.161

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com