



## Gleam Pendant – White

Experience the enchanting glow of Gleam, a bulb-based pendant light, designed by Sebastian Bergne. With a unique heptagon-inspired look, you can choose from the inflated design for a bold, dimensional effect, or the deflated design for sleek sophistication. Available in three sizes, each design aligns with the 3D print grain for a seamless aesthetic. Plus, the printed parts are made with ISCC Plus certified bio-circular material, making them an environmentally conscious choice. Whether you're looking to create a cozy atmosphere in your home or add a unique feature to your hospitality venue, Gleam is the perfect addition.

### General Information

|                 |         |
|-----------------|---------|
| Warranty period | 5 years |
|-----------------|---------|

### Operating and Electrical

|                      |                 |
|----------------------|-----------------|
| Input Voltage        | 220 to 240 V    |
| Line Frequency       | 50 to 60 Hz     |
| Protection class IEC | Safety class II |

## Mechanical and Housing

|                                     |                         |
|-------------------------------------|-------------------------|
| Housing Material                    | Polycarbonate           |
| Housing Color                       | White                   |
| Overall length                      | 220 mm                  |
| Overall width                       | 220 mm                  |
| Overall height                      | 225 mm                  |
| Overall diameter                    | 220 mm                  |
| Dimensions (Height x Width x Depth) | 225 x 220 x 220 mm      |
| Ingress protection code             | IP20 [Finger-protected] |
| Mech. impact protection code        | IK02 [0.2 J standard]   |
| Mounting                            | Suspended               |
| Net Weight (Piece)                  | 0.932 kg                |
| Cable color                         | black                   |

## Product Data

|                                 |                                            |
|---------------------------------|--------------------------------------------|
| Order product name              | DL GL1S PT E27 OT432WH300<br>ASI400 FBK BK |
| Full product name               | DL GL1S PT E27 OT432WH300<br>ASI400 FBK BK |
| Full product code               | 872016986626300                            |
| Order code                      | 86626300                                   |
| Material Nr. (12NC)             | 912500108963                               |
| Numerator - Quantity Per Pack   | 1                                          |
| EAN/UPC - Product/Case          | 8720169866263                              |
| Numerator - Packs per outer box | 1                                          |
| EAN/UPC - Case                  | 8720169866263                              |

## Approval and Application

|                   |                                   |
|-------------------|-----------------------------------|
| Glow-wire test    | Temperature 650 °C, duration 30 s |
| CE mark           | Yes                               |
| EU RoHS compliant | No                                |

## Dimensional drawing

